



PW6030 SCALE



CARE OF YOUR SCALES

Place your scale on a flat surface.
Stand gently, display will vary if you move.
Do not use abrasive detergent.
Adjust dial to zero before use.
Accuracy is guaranteed as the tolerance limit below:
0~80Kg (0 ~ 175lb) ± 1.2d
>80Kg (175lb) ± 2.0d



PW6030 PESAPERSONA
PCS
MISURE: 34,5 x 27,5 x 13 cm
PESO: 3 kg



Cartone riciclabile | Recyclable cardboard
dcg16.it



PW6030 SCALE

minum
0,05 kg

max capacity
160 kg

Mechanical scale
Easy to read quadrant
Measuring up to 160 Kg
Minimum effective 0,05 Kg
Dimensions: 34,5 x 27,5 x 13 cm
Weight: 3 Kg



dcg16.it



PW6030 PESAPERSONA



ISTRUZIONI

Posiziona la bilancia su una superficie piatta.
Sali con cautela, il quadrante di indicazione varierà se ti muovi.
Per la pulizia, non usare detergenti abrasivi.
Regola la lancetta del quadrante sullo zero prima dell'utilizzo.
La precisione è garantita come riportato:
0~80Kg (0 ~ 175lb) ± 1.2d
>80Kg (175lb) ± 2.0d



8 032774 621312



Cartone riciclabile | Recyclable cardboard
dcg16.it



PW6030 PESAPERSONA

minimo
0,05 kg

capacità max
160 kg

Bilancia meccanica
Grande quadrante leggibile
Misurazione fino a 160 Kg
Minimo effettivo 0,05 Kg
Dimensioni: 34,5 x 27,5 x 13 cm
Peso: 3 Kg



dcg16.it

